

# KeepPulse



## Operating Conditions

Maximum working pressure	150 psi (10.3 bar)
Minimum recommended pressure	40 psi (2.8 bar)

- ◆ Values defined based on the components used in the line, such as valves, sensors, and hoses.
- ◆ Generated flows and pulse frequency depend on the specific configuration of each installed unit, variables that respond to the particular setup.

## Features

### » Remote, real-time dosing.

Precise adjustment and digital activation of oxygen flow.

### » Automatic calculation of O<sub>2</sub> metabolic requirements.

With preloaded curves based on average fish weight, number of fish, and water temperature.

### » Remote and centralized supervision.

Monitoring from a digital platform.

### » Fault detection and automatic alerts.

Sends notifications for timely response.

### » Traceability and data.


Reporting of oxygen consumption and critical system variables.

### » Homogeneous diffusion.

Controlled pressure pulses enabling uniform oxygen injection throughout the cage.

Remote and real-time oxygenation control for maximum efficiency.


KeepPulse optimizes oxygenation in aquaculture operations through real-time remote regulation of oxygen flows. It analyzes key variables to optimize oxygen supply in each cage, enabling monitoring from a centralized platform. It also detects anomalies in real time, sending alerts and generating detailed reports to support operational decision-making.





# KeepPulse System Diagram

- |   |                     |   |                                  |
|---|---------------------|---|----------------------------------|
| 1 | Pressure transducer | 4 | Solenoid valves                  |
| 2 | Temperature sensor  | 5 | Pressure transducer              |
| 3 | Flow limiter        | 6 | PLC monitoring and control panel |



**Integration with existing infrastructure.**  
Compatible with multiple systems.

# KeepPulse

